




Part Number : [878580750](#)
Product Description : 2.00mm Pitch Milli-Grid
Breakaway Header, Surface Mount, Single Row,
Parallel, 2.54µm Tin (Sn) Plating, without Peg, with
Pick-and-Place Polyimide Tape, Mating Pin Length
3.20mm , 7 Circuits, Lead-Free
Series Number : 87858
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[878580750 sd.pdf](#)
[PK-87858-300-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[503940001-AS-000.pdf](#)
[PS-87761-100-001.pdf](#)
[877610000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	87858
Description	2.00mm Pitch Milli-Grid Breakaway Header, Surface Mount, Single Row, Parallel, 2.54µm Tin (Sn) Plating, without Peg, with Pick-and-Place Polyimide Tape, Mating Pin Length 3.20mm , 7 Circuits, Lead-Free
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	Milli-Grid
UPC	883906047849

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	2.0A
-------------------------------	------

Voltage - Maximum	125V
-------------------	------

Physical

Breakaway	Yes
Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	3.20mm
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.263/g
Number of Rows	1
Orientation	Parallel
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.80mm
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Shrouded	No
Stackable	No
Temperature Range - Operating	-55° to +105°C

Termination Interface Style	Surface Mount
-----------------------------	---------------

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	2.00mm Single Row Receptacles