



Part Number : [797582140](#)
Product Description : Pre-Crimped Lead Nano-Fit
Female-to-Nano-Fit Female, Matte Tin (Sn) Plating,
300.00mm Length, 20 AWG, Black
Series Number : 79758
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[797582140 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	79758
Description	Pre-Crimped Lead Nano-Fit Female-to-Nano-Fit Female, Matte Tin (Sn) Plating, 300.00mm Length, 20 AWG, Black
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Nano-Fit Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	Nano-Fit
UPC	193264154814

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Net Weight	2.167/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	20

Mates With / Use With

Use with Part(s)

Description	Part Number
Nano-Fit TPA Capable Single Row Receptacle Housings	<u>105307</u>
Nano-Fit TPA Capable Dual Row Receptacle Housings	<u>105308</u>
Nano-Fit BMI TPA Capable Plug Housings	<u>224556</u>