


**Part Number: 95502-2663**

Modular Jack, Through Hole Version, Bottom Entry, 6/6 Circuits



Series image - Reference only

Status:	OBSOLETE
Replacement:	955027663
Series:	95502
Category:	Modular Jacks/Plugs
Overview:	Modular Plugs - Jacks

Mates With Part(s):[90075](#) FCC 68 Plug**Product Environmental Compliance****EU RoHS:** ELV and RoHS Compliant**China RoHS:** **REACH SVHC:** Contains SVHC: No**Low-Halogen Status:** Not Reviewed**Part Detail****General**

Status	Obsolete
Category	Modular Jacks/Plugs
Series	95502
Component Type	PCB Jack
Magnetic	No
Overview	Modular Plugs - Jacks
Performance Category	3
Power over Ethernet (PoE)	N/A
Product Name	RJ11

Physical

Boot Color	N/A
Color - Resin	Black
Durability (mating cycles max)	250
Flammability	94V-0
Inverted / Top Latch	N/A
Jack Height	12.58mm
Lightpipes/LEDs	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Orientation	Bottom Entry
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	1.02mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	1.270µm
Plating min - Termination	1.905µm
Ports	1
Positions / Loaded Contacts	6/6
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +80°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire/Cable Type	N/A

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	1.5A
Shielded	No
Voltage - Maximum	125V DC

Agency Certification

UL	E107635
----	---------

Material Info

UPC	800756915753
-----	--------------

Reference - Drawing Numbers

Product Specification	PS-95502-001
-----------------------	--------------

Sales Drawing

SD-95502-001

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)