

HONEYWELL

See full Datasheet below...

onlinecomponents.com
THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

BUY NOW


 **MASTER**TM
E L E C T R O N I C S

BUY NOW

masterelectronics.com & onlinecomponents.com
are **authorized** e-commerce distributors
of electronic components.

HONEYWELL
PART NUMBER
11CX12HM-D01E

REV	DOCUMENT	CHANGED BY	CHECK
B	0057849	MBH 22OCT09	CMH



NOTES

- 1 - EXPLOSION PROOF - AUSTRALIA APPROVAL Ex d IIC IP66/IP67 T6 (-40°C < T_a < +70°C) OR Ex tD A21
- 2 - EUROPEAN HAZARDOUS LOCATIONS DESIGNATION: EExd IIC T6 CATEGORY II 2 GD
- 3 - ALUMINUM ENCLOSURE FINISHED WITH BLUE AND BLACK EPOXY PAINT
- 4 - 6-32 UNC X (7.92) PAN HEAD TERMINAL SCREW AND LOCKWASHER (.312) (SEMS TERMI-LOX) (3 PER BASIC)
- 5 - CAMS MAY BE REPOSITIONED IN 7°20' INCREMENTS
- 6 - 2 BASICS; EACH OPERATES CLOCKWISE AND COUNTER CLOCKWISE
- 7 - FOR USE IN TEMPERATURES UP TO 85°C
- 8 - WEIGHT: 2.49 LB (1.13 Kg) APPROX
- 9 - UNIT PROVIDES NO SHAFT RESTORING FORCE. THE ACTUATING DEVICE MUST CONTROL MOVEMENT OF SHAFT

CHARACTERISTICS	ELECTRICAL DATA
OPERATING TORQUE..... 0.37 LB FT (0.50 Nm) MAX	CONTACT ARRANGEMENT
PRETRAVEL..... 15° MAX	S P D T (EACH BASIC)
DIFFERENTIAL TRAVEL..... 10° MAX	L96
OVERTRAVEL..... 90° MIN	15A 125, 250 OR 480 VAC
	1/8HP 125 VAC, 1/4HP 250 VAC
	1/2A 125 VDC, 1/4A 250 VDC
	Ex CE

DESIGN UNITS: MM/INCH	DRAWN	KNS	05OCT06
TOLERANCES UNLESS NOTED:	CHECK	DVM	05OCT06
NO PLACES	x	±	.040
ONE PLACE	.x	±	.030
TWO PLACE	.xx	±	.015
THREE PLACE	.xxx	±	.005
ANGLES	x	±	-
THIRD ANGLE PROJECTION			

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.	
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY	Pro/ENGINEER

Honeywell			
TITLE SWITCH, ENCLOSED			
SIZE	TYPE	DRAWING NAME	REV
C	I	11CX12HM-D01E	B
SCALE	1:1	WEIGHT	SHEET 1 OF 1