



HONEYWELL

CMC25.5

See full Datasheet below...

onlinecomponents.com

THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

BUY NOW



MASTERTM
ELECTRONICS

BUY NOW

masterelectronics.com & onlinecomponents.com
are **authorized** e-commerce distributors
of electronic components.



Home > Products > Wirewound Resistors > CMC > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

CMC25.5



Actual product appearance may vary.

CMC Series, 0.5 Ohms, 25.0 W, Fixed, Wirewound Resistor

Features

All molded and welded construction
Screw mounts on chassis surface
Heat-sink capability
Protection against extreme environments
Exceeds MIL-R-18546 standards

Potential Applications

Harsh environments
High temperature
Load adjustors for power amplifiers

Description

The CMC Series resistors are exceptionally stable and versatile. The anodized aluminum housing provides durability to withstand shock, vibration and harsh environmental conditions. It also offers heat-sinking capabilities and chassis mounting options. The terminals are copperweld, tinned with axial leads. Made to MIL-R-18546 standards, the CMC series provides durability with superior power ratings.

Note: Not suitable for high frequency applications.

Supporting Documentation

[Dimensions](#)

Product Specifications	
Resistor Type	Fixed
Power Rating	25 W
Resistance Value	0.5 Ohms
Terminal Type	Lug
Housing Material	Aluminum
Tolerance	± 5%
Temperature Coefficient	± 90 ppm/ °C
Availability	Global
UNSPSC Code	32121608
UNSPSC Commodity	32121608 Wire Wound Resistor
Series Name	CMC

My Links

[Login to iCOM](#)
[Login as Rep/AD](#)
[Login as Guest](#)
[Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

[Specification Search](#)