




Home > Products > MICRO SWITCH™ Toggle Switches > TW > Product Page

112TW401-5



Actual product appearance may vary.

TW Series Toggle Switch, 2 pole, 3 position, IWTS terminal, Tab Lever

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

Features

Save space and weight
 SPDT and DPDT circuitry
 Temperature range: -85° F to +160° F (-65° C to +71° C)
 Sealed bushing versions
 Choice of 1/8 in. or 15/32 in. bushing
 Color tab available on 15/32 in. bushing
 UL recognized

Potential Applications

Industrial machinery and equipment
 Military and commercial aviation
 Construction equipment
 Test instruments
 Agricultural machinery
 Process control
 Medical instrumentation

Description

MICRO SWITCH™ miniature toggle switches in two bushing sizes. Molded in terminals are plated for soldering. Momentary and maintained circuitry closures available. Special on-on-on circuitries are also available. Pull-to-unlock levers prevent accidental operation.

Supporting Documentation

- ▣ [Accessory: Lever Sleeve](#)
- ▣ [Accessory: Seals](#)
- ▣ [Accessory: Nuts](#)
- ▣ [Engineering Drawing](#)

Product Specifications			
Circuitry/Operating action	Keyway	Center Position	Opposite Keyway Position
	Momentary Position	Position	Position
Product Type	MICRO SWITCH™ Toggle Switch		
Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vac to 115 Vac, 0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc		
Circuitry	DPDT		
Action	3 position		
Mounting	Bushing 15/32 in		
Termination	IWTS		
Lever Type	Tab		
Comment	Fine silver contacts		
Availability	Global		
UNSPSC Code	30211908		
UNSPSC Commodity	30211908 Toggle switches		
Series Name	TW		

My Links

- [Login to iCOM](#)
- [Login as Rep/AD](#)
- [Login as Guest](#)
- [Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

[Specification Search](#)