



Home > Products > Piezoresistive Silicon > XCAL > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

XCAL4010GN



Actual product appearance may vary.

Pressure Sensors: Measurement Type: Differential, Gage, Vacuum Gage; Signal Conditioning: Unamplified; Pressure Range: 0 in H₂O to 10.0 in H₂O; Port Style: Barbed

Features

Precise Temperature Compensation
 Low cost
 High Performance
 Gage, Absolute and Differential Versions
 Constant Voltage Excitation
 Calibrated Output
 Ratiometric Output Voltage

Potential Applications

Ventilators
 CPAP
 Audiometers
 Air Compressors
 Chemical Analyzers
 VAV Controller
 Airflow

Description

The XCA Series of pressure sensors use state of the art silicon micromachined pressure sensors in conjunction with stress free packaging techniques to provide highly accurate, amplified, calibrated and temperature compensated pressure sensors for the most demanding applications.

Supporting Documentation

[Dimensions](#)

[Equivalent Circuit, Pin Designations](#)

[Engineering Drawing](#)

Product Specifications	
Measurement Type	Differential, Vacuum Gage, Gage
Signal Conditioning	Amplified
Pressure Range	0 in H ₂ O to 10.0 in H ₂ O
Maximum Overpressure	100 in H ₂ O
Supply Voltage	3.0 Vdc min., 5.0 Vdc typ., 16.0 Vdc max.
Compensated	Yes
Output Calibration	Yes
Termination	PCB
Port Style	Barbed
Package Style	Honeywell DI - XCA
Typical Sensitivity	0.4 V/in H ₂ O
Full Scale Span	4.0 Vdc typ.
Null Offset	0.25 Vdc typ.
Null Shift over Temperature	± 1% Span
Span Shift Over Temperature	± 1.0% span
Linearity, Hysteresis Error	± 0.5 % Span
Operating Temperature Range	-25 °C to 85 °C [-13 °F to 185 °F]
Compensated Temperature Range	0 °C to 50 °C [32 °F to 122 °F]
Storage Temperature Range	-40 °C to 125 °C [-40 °F to 257 °F]
Media Compatibility	Port 1: Dry gases only. Media must be compatible with epoxy based adhesive. Port 2: Wetted materials. Media must be compatible with nylon housing, epoxy adhesive and silicon.
UNSPSC Code	411121
UNSPSC Commodity	411121 Transducers
Availability	Global
Series Name	XCAL

My Links

[Login to iCOM](#)
[Login as Rep/AD](#)
[Login as Guest](#)
[Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

[Specification Search](#)