



HONEYWELL

XPX100GFS

See full Datasheet below...

onlinecomponents.com

THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

BUY NOW



MASTERTM
ELECTRONICS

BUY NOW

masterelectronics.com & onlinecomponents.com
are **authorized** e-commerce distributors
of electronic components.



Home > Products > Piezoresistive Silicon > XPX > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

XPX100GFS



Actual product appearance may vary.

Pressure Sensors: Measurement Type: Gage, Vacuum Gage; Signal Conditioning: Unamplified; Pressure Range: #177 100.0 psi; Port Style: Barbed

Features

Low Cost, Small Size
 Temperature Compensated
 Zero and Span Calibrated
 MilliVolt Output
 Gage, Differential, and Absolute Pressure
 Constant Voltage Excitation
 High Impedance- Low Current

Potential Applications

Medical Applications
 Applications Requiring Small Size
 Applications Requiring Vacuum, Positive Pressure or Both

Description

The XPXL/XPX and XPCL/XPC Series sensors integrate silicon micromachined sensing technology, temperature compensation, and calibration in a complete family of low cost packages. This series offers the most cost-effective solution for design requirements. These piezoresistive pressure sensors use micromachined silicon chips mounted on a ceramic and protected with a plastic cap. Several tube arrangements with nylon housings are available for various pressure applications. On devices of 5 psi and above, the topside of the chip is protected against humidity by a Silgel coating. While the sensors are designed for use with noncorrosive, nonionic pressure media, they accommodate many gases that are used in medical applications.

Supporting Documentation

[Dimensions](#)

[Equivalent Circuit, Pin Designations](#)

[Engineering Drawing](#)

Product Specifications	
Measurement Type	Vacuum Gage, Gage
Signal Conditioning	Unamplified
Pressure Range	± 100 psi
Maximum Overpressure	250 psi
Supply Voltage	3.0 Vdc min., 12.0 Vdc typ., 16.0 Vdc max.
Compensated	No
Output Calibration	No
Termination	PCB
Port Style	Barbed
Package Style	Honeywell DI - XPX
Typical Sensitivity	7.08 mV/psi
Full Scale Span	295 mV typ.
Null Offset	0 mV typ.
Null Shift over Temperature	2500 ppm/°C
Span Shift Over Temperature	- 1800 ppm/°C
Linearity, Hysteresis Error	± 1.0 % max.Span
Input Resistance	2600 ppm/°C
Output Resistance	- 1800 ppm/°C
Operating Temperature Range	-25 °C to 85 °C [- 13 °F to 185 °F]
Storage Temperature Range	- 40 °C to 125 °C [- 40 °F to 257 °F]
Media Compatibility	Port 1: Dry gases only. Media must be compatible with epoxy based adhesive. Port 2: Wetted materials. Media must be compatible with nylon housing, epoxy adhesive and silicon.
UNSPSC Code	411121
UNSPSC Commodity	411121 Transducers
Availability	Global
Series Name	XPX

My Links

[Login to iCOM](#)
[Login as Rep/AD](#)
[Login as Guest](#)
[Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

[Specification Search](#)