



ELECTRONICS, INC.
 44 FARRAND STREET
 BLOOMFIELD, NJ 07003
 (973) 748-5089
<http://www.nteinc.com>

NTE74S05 Integrated Circuit TTL – Hex Inverter with Open Collector Outputs

Description:

The NTE74S05 contains six independent inverters in a 14-Lead plastic DIP type package. The open collector outputs require pull-up resistors to perform correctly. They may be connected to other open collector outputs to implement active-low wired-OR or active-high wired-AND functions. Open collector devices are often used to generate higher V_{OH} levels.

Absolute Maximum Ratings: (Note 1)

Supply Voltage, V_{CC} 7V
 DC Input Voltage, V_{IN} 5.5V
 Off-State Voltage 7V
 Operating Temperature Range, T_A 0°C to +70°C
 Storage Temperature Range, T_{stg} -65°C to +150°C

Note 1. Unless otherwise specified, all voltages are referenced to GND.

Recommended Operating Conditions:

Parameter	Symbol	Min	Typ	Max	Unit
Supply Voltage	V_{CC}	4.75	5.0	5.25	V
High-Level Input Voltage	V_{IH}	2.0	-	-	V
Low-Level Input Voltage	V_{IL}	-	-	0.8	V
High-Level Output Voltage	V_{OH}	-	-	5.5	V
Low-Level Output Current	I_{OL}	-	-	20	mA
Operating Temperature Range	T_A	0	-	+70	°C

Electrical Characteristics: (Note 2, Note 3)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Input Clamp Voltage	V_{IK}	$V_{CC} = \text{MIN}, I_I = -18\text{mA}$	-	-	-1.2	V
High Level Output Current	I_{OH}	$V_{CC} = \text{MIN}, V_{IL} = 0.8\text{V}, V_{OH} = -5.5\text{V}$	-	-	0.25	mA
Low Level Output Voltage	V_{OL}	$V_{CC} = \text{MIN}, V_{IH} = 2\text{V}, I_{OL} = 20\text{mA}$	-	-	0.5	V
Input Current	I_I	$V_{CC} = \text{MAX}, V_I = 5.5\text{V}$	-	-	1	mA

Note 2. For conditions shown as MIN or MAX, use the appropriate value specified under “Recommended Operation Conditions”.

Note 3. All typical values are at $V_{CC} = 5\text{V}, T_A = +25^\circ\text{C}$.

Electrical Characteristics (Cont'd): (Note 2, Note 3)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
High Level Input Current	I_{IH}	$V_{CC} = \text{MAX}, V_I = 2.7\text{V}$	-	-	50	μA
Low Level Input Current	I_{IL}	$V_{CC} = \text{MAX}, V_I = 0.5\text{V}$	-	-	-2	mA
High Level Supply Current	I_{CCH}	$V_{CC} = \text{MAX}, V_I = 0$	-	9.0	19.8	mA
Low Level Supply Current	I_{CCL}	$V_{CC} = \text{MAX}, V_I = 4.5\text{V}$	-	30	54	mA

Note 2. For conditions shown as MIN or MAX, use the appropriate value specified under "Recommended Operation Conditions".

Note 3. All typical values are at $V_{CC} = 5\text{V}, T_A = +25^\circ\text{C}$.

Note 4. Not more than one output should be shorted at a time, and the duration of the short-circuit should not exceed one second.

Switching Characteristics: ($V_{CC} = 5\text{V}, T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Propagation Delay Time From A Input to Y Output)	t_{PLH}	$R_L = 280\Omega, C_L = 15\text{pF}$	2.0	5.0	7.5	ns
	t_{PHL}		2.0	4.5	7.0	ns
	t_{PLH}	$R_L = 280\Omega, C_L = 50\text{pF}$	-	7.5	-	ns
	t_{PHL}		-	7.0	-	ns

Function Table (Each Inverter):

Input	Output
A	Y
H	L
L	H

H = HIGH Voltage Level

L = LOW Voltage Level

Pin Connection Diagram



