



Part Number : [930700011](#)
Product Description : Appli-Mate RAST 2.5 Header,
Vertical, 3 Circuits, Tin (Sn) Plating, Glow-Wire Capable,
No Blocked Positioning Keys, Natural
Series Number : 93070
Status : Active
Product Category : PCB Headers and Receptacles

Documents and Resources

Drawings

- [930700011 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)
- [Symbol and Footprint \(Multi-Format\)](#)

Specifications

- [PK-90871-001-001.pdf](#)
 - [PK-93070-001-001.pdf](#)
 - [PS-93070-001-001.pdf](#)
 - [PS-99020-0040-001.pdf](#)
-

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	93070
Description	Appli-Mate RAST 2.5 Header, Vertical, 3 Circuits, Tin (Sn) Plating, Glow-Wire Capable, No Blocked Positioning Keys, Natural
Application	Wire-to-Board
Comments	This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12 and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. The customers

	using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.
Component Type	PCB Header
Product Name	RAST 2.5
UPC	884982381322

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	32V

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	No

Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.030/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.50mm
PC Tail Length	3.30mm
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	3.048µm
Plating min - Termination	3.048µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-20° to +120°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.50mm Pitch Appli-Mate RAST 2.5 IDT Housings	<u>91716</u>
2.50mm Pitch Appli-Mate RAST 2.5 Female Connectors	<u>93050</u>

Use with Part(s)

Description	Part Number
Use With	RAST Standard Interface

Application Tooling

Global

Description	Part Number
RAST 2.5 and R-Power Semi-Automatic IDC Machine	<u>2166580100</u>