

# FDS4465

## P-Channel 1.8V Specified POWERTRENCH<sup>®</sup> MOSFET

### Description

This P-Channel 1.8 V specified MOSFET is a rugged gate version of ON Semiconductor's advanced POWERTRENCH process. It has been optimized for power management applications with a wide range of gate drive voltage (1.8 V – 8 V).

### Features

- -13.5 A, -20 V
  - ◆  $R_{DS(ON)} = 8.5 \text{ m}\Omega @ V_{GS} = -4.5 \text{ V}$
  - ◆  $R_{DS(ON)} = 10.5 \text{ m}\Omega @ V_{GS} = -2.5 \text{ V}$
  - ◆  $R_{DS(ON)} = 14 \text{ m}\Omega @ V_{GS} = -1.8 \text{ V}$
- Fast Switching Speed
- High Performance Trench Technology for Extremely Low  $R_{DS(ON)}$
- High Current and Power Handling Capability

### Applications

- Power Management
- Load Switch
- Battery Protection

### Specifications

#### ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

| Symbol         | Parameter  | Value                | Unit             |
|----------------|--|----------------------|------------------|
| $V_{DSS}$      | Drain-to-Source Voltage                          | -20                  | V                |
| $V_{GSS}$      | Gate-to-Source Voltage                           | $\pm 8$              | V                |
| $I_D$          | Drain Current                                    | Continuous (Note 1a) | -13.5            |
|                |  | Pulsed               | -50              |
| $P_D$          | Power Dissipation                                | (Note 1a)            | 2.5              |
|                |  | (Note 1b)            | 1.5              |
|                |  | (Note 1c)            | 1.2              |
| $T_J, T_{STG}$ | Operating and Storage Junction Temperature Range | -55 to +175          | $^\circ\text{C}$ |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

### THERMAL CHARACTERISTICS

| Symbol          | Parameter   | Value | Unit                      |
|-----------------|---|-------|---------------------------|
| $R_{\theta JA}$ | Thermal Resistance, Junction-to-Ambient (Note 1a) | 50    | $^\circ\text{C}/\text{W}$ |
| $R_{\theta JA}$ | Thermal Resistance, Junction-to-Ambient (Note 1c) | 125   | $^\circ\text{C}/\text{W}$ |
| $R_{\theta JC}$ | Thermal Resistance, Junction-to-Ambient (Note 1)  | 25    | $^\circ\text{C}/\text{W}$ |





ON Semiconductor<sup>®</sup>


[www.onsemi.com](http://www.onsemi.com)

| $V_{DSS}$ | $R_{DS(on)}$ MAX         | $I_D$ MAX |
|-----------|--------------------------|-----------|
| -20 V     | 8.5 m $\Omega$ @ -4.5 V  | -13.5 A   |
|           | 10.5 m $\Omega$ @ -2.5 V |           |
|           | 14 m $\Omega$ @ -1.8 V   |           |

### P-Channel



### MARKING DIAGRAM



A = Assembly Site  
 L = Wafer Lot Number  
 YW = Assembly Start Week  
 FDS4465 = Specific Device Code

### ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

# FDS4465

## ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

| Symbol                         | Parameter                                 | Test Condition   | Min | Typ | Max  | Unit                 |
|--------------------------------|---|--|-----|-----|------|----------------------|
| $BV_{DSS}$                     | Drain-Source Breakdown Voltage            | $V_{GS} = 0\text{ V}, I_D = 250\ \mu\text{A}$                | -20 |     |      | V                    |
| $\Delta BV_{DSS} / \Delta T_J$ | Breakdown Voltage Temperature Coefficient | $I_D = -250\ \mu\text{A}$ , Referenced to $25^\circ\text{C}$ |     | -12 |      | mV/ $^\circ\text{C}$ |
| $I_{DSS}$                      | Zero Gate Voltage Drain Current           | $V_{DS} = -16\text{ V}, V_{GS} = 0\text{ V}$                 |     |     | -1   | $\mu\text{A}$        |
| $I_{GSSF}$                     | Gate-Body Leakage, Forward                | $V_{GS} = 8\text{ V}, V_{DS} = 0\text{ V}$                   |     |     | 100  | nA                   |
| $I_{GSSR}$                     | Gate-Body Leakage, Reverse                | $V_{GS} = -8\text{ V}, V_{DS} = 0\text{ V}$                  |     |     | -100 | nA                   |

## ON CHARACTERISTICS (Note 2)

|                                  |  |  |                           |      |      |                      |
|----------------------------------|--|--|---------------------------|------|------|----------------------|
| $V_{GS(th)}$                     | Gate Threshold Voltage                         | $V_{DS} = V_{GS}, I_D = 250\ \mu\text{A}$                    | -0.4                      | -0.6 | -1.5 | V                    |
| $\Delta V_{GS(th)} / \Delta T_J$ | Gate Threshold Voltage Temperature Coefficient | $I_D = -250\ \mu\text{A}$ , Referenced to $25^\circ\text{C}$ |                           | 3    |      | mV/ $^\circ\text{C}$ |
| $R_{DS(on)}$                     | Static Drain-Source On-Resistance              | $V_{GS} = -4.5\text{ V}, I_D = -13.5\text{ A}$               |                           | 6.7  | 8.5  | m $\Omega$           |
|                                  |  | $V_{GS} = -2.5\text{ V}, I_D = -12\text{ A}$                 |                           | 8.0  | 10.5 |                      |
|                                  |  | $V_{GS} = -1.8\text{ V}, I_D = -10.5\text{ A}$               |                           | 9.8  | 14   |                      |
|                                  |  | $V_{GS} = -4.5\text{ V}, I_D = -13.5\text{ A}$               | $T_J = 125^\circ\text{C}$ | 9.0  | 13   |                      |
| $I_{D(on)}$                      | On-State Drain Current                         | $V_{GS} = -4.5\text{ V}, V_{DS} = -5\text{ V}$               | -50                       |      |      | A                    |
| $g_{FS}$                         | Forward Transconductance                       | $V_{DS} = -5\text{ V}, I_D = -13.5\text{ A}$                 |                           | 70   |      | S                    |

## DYNAMIC CHARACTERISTICS

|           |                              |  |     |      |     |          |
|-----------|------------------------------|--|-----|------|-----|----------|
| $C_{iss}$ | Input Capacitance            | $V_{DS} = -10\text{ V}, V_{GS} = 0\text{ V}, f = 1.0\text{ MHz}$ |     | 8237 |     | pF       |
| $C_{oss}$ | Output Capacitance           |  |     | 1497 |     | pF       |
| $C_{rss}$ | Reverse Transfer Capacitance |  |     | 750  |     | pF       |
| $R_g$     | Gate Resistance              |  | 0.1 | 3.0  | 6.0 | $\Omega$ |

## SWITCHING CHARACTERISTICS (Note 2)


|              |                     |   |  |     |     |    |
|--------------|---------------------|---|--|-----|-----|----|
| $t_{d(on)}$  | Turn-On Delay Time  | $V_{DD} = -10\text{ V}, I_D = -1\text{ A}, V_{GS} = -4.5\text{ V}, R_{GEN} = 6\ \Omega$ |  | 20  | 36  | ns |
| $t_r$        | Turn-On Rise Time   |   |  | 24  | 38  | ns |
| $t_{d(off)}$ | Turn-Off Delay Time |   |  | 300 | 480 | ns |
| $t_f$        | Turn-Off Fall Time  |   |  | 140 | 224 | ns |
| $Q_g$        | Total Gate Charge   | $V_{DS} = -10\text{ V}, I_D = -1\text{ A}, V_{GS} = -4.5\text{ V}$                      |  | 86  | 120 | nC |
| $Q_{gs}$     | Gate-Source Charge  |   |  | 20  |     | nC |
| $Q_{gd}$     | Gate-Drain Charge   |   |  | 11  |     | nC |

## DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS


|          |   |   |  |      |      |   |
|----------|---|---|--|------|------|---|
| $I_S$    | Maximum Continuous Drain-Source Diode Forward Current |   |  | -2.1 | A    |   |
| $V_{SD}$ | Drain-Source Diode Forward Voltage                    | $V_{GS} = 0\text{ V}, I_S = -2.1\text{ A}$ (Note 2) |  | -0.6 | -1.2 | V |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.


- $R_{\theta JA}$  is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins.  $R_{\theta JC}$  is guaranteed by design while  $R_{\theta CA}$  is determined by the user's board design.



a)  $50^\circ\text{C/W}$  when mounted on a  $1\text{ in}^2$  pad of 2 oz copper



b)  $105^\circ\text{C/W}$  when mounted on a  $.04\text{ in}^2$  pad of 2 oz copper



c)  $125^\circ\text{C/W}$  when mounted on a minimum pad

Scale 1:1 on letter size paper

- Pulse Test: Pulse Width  $< 300\ \mu\text{s}$ , Duty Cycle  $< 2.0\%$

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage




Figure 3. On-Resistance Variation with Temperature




Figure 4. On-Resistance Variation with Gate-to-Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature

TYPICAL CHARACTERISTICS




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance Characteristics




Figure 9. Maximum Safe Operating Area




Figure 10. Single Pulse Maximum Power Dissipation




Figure 11. Transient Thermal Response Curve

Thermal characterization performed using the conditions described in Note 1c.  
 Transient thermal response will change depending on circuit board design.

# FDS4465

## PACKAGE MARKING AND ORDERING INFORMATION

| Device Marking | Device  | Reel Size | Tape Width | Shipping <sup>†</sup> |
|----------------|---------|-----------|------------|-----------------------|
| FDS4465        | FDS4465 | 13"       | 12 mm      | 2500 / Tape & Reel    |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

POWERTRENCH is registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.







**MECHANICAL CASE OUTLINE**  
**PACKAGE DIMENSIONS**

ON Semiconductor®



**SOIC8**  
**CASE 751EB**  
**ISSUE A**

DATE 24 AUG 2017



- NOTES:
- A) THIS PACKAGE CONFORMS TO JEDEC MS-012, VARIATION AA.
  - B) ALL DIMENSIONS ARE IN MILLIMETERS.
  - C) DIMENSIONS DO NOT INCLUDE MOLD FLASH OR BURRS.
  - D) LANDPATTERN STANDARD: SOIC127P600X175-8M

**DETAIL A**  
 SCALE: 2:1

|                         |                                  |  |
|-------------------------|----------------------------------|--|
| <b>DOCUMENT NUMBER:</b> | <b>98AON13735G</b>               | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>STATUS:</b>          | <b>ON SEMICONDUCTOR STANDARD</b> |  |
| <b>NEW STANDARD:</b>    |                                  |  |
| <b>DESCRIPTION:</b>     | <b>SOIC8</b>                     | <b>PAGE 1 OF 2</b>   |



ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Email Requests to: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

ON Semiconductor Website: [www.onsemi.com](http://www.onsemi.com)

### TECHNICAL SUPPORT

North American Technical Support:  
Voice Mail: 1 800-282-9855 Toll Free USA/Canada  
Phone: 011 421 33 790 2910

### Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative