

Pressure Switch - 77343XX (/sensing.honeywell.com/product-page?pr_id=)

(Home (/) : Products (/products) : Switches : Pressure and Vacuum Switches : Pressure Switch : 5000)

Distributor Inventory

Input part number for stock availability



5000 Series vacuum switch with direct action blade contacts

Actual product appearance may vary.

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#)

[Specs](#)

[Documentation](#)

Product Specifications

Product Type	Vacuum Switch
Electrical Termination	#8-32 screw
Contact Setting Range	1.1 in-Hg to 22 in-Hg
Standard Factory Set Points	1.1 in-Hg, 2 in-Hg, 4 in-Hg, 6 in-Hg, 10 in-Hg, 13 in-Hg, 15 in-Hg, 17in-Hg, 20 in-Hg, 22 in-Hg, 24 in H2O, 25 in H2O, & 28 in H2O
Circuitry	SPST-NC
Contact(s)	Silver alloy, gold plated
Burst Pressure	150 psi
Operating Pressure	30 in-Hg max.
Resistive Ratings	15 A, 6 Vdc; 8 A, 12 Vdc; 4 A, 24 Vdc
Inductive Ratings	1 A, 120 Vac; 0.5 A, 240 Vac
Standard Seal	Nitrile O-ring
Diaphragm	Fluorosilicone elastomer
Temperature	-40 °F to 250 °F
Base	Brass
Cover Type	Glass reinforced polyester
Options	Steel, plastic, or stainless steel base; various base connector thread sizes; wire leads (potted and sealed)
Connector(s)	1/8-27 NPT male thread
Availability	Global
Comment	XX indicates set point
Series Name	5000

Narrow Your Search

Modify Your Search

Products

Select Option

Technology

Select Option

Industries Served

Select Option

Product Search

Product Type:

New Products Only

Industry: All Industries

Entire Product Catalog

Search Term: Start Here ...

Search

My Links


- [eCOM Login \(/index.php?ci_id=50629&la_id=1\)](#)
- [Request Access to eCOM \(/ecom-access-request\)](#)
- [Rep/AD Portal Login \(/index.php?ci_id=50606&la_id=1\)](#)
- [Rep/AD Portal Access Request \(/index.php?ci_id=50630&la_id=1\)](#)
- [Sample Request \(/samplerequest\)](#)
- [Digital U - HWL Learning Hub Login \(/index.php?ci_id=50607&la_id=1\)](#)
- [Limitless Microsite \(/index.php?ci_id=50631&la_id=1\)](#)
- [Supplier Microsite \(/index.php?ci_id=44887&la_id=1\)](#)

Literature and Media

- [Data Sheets \(/white-paper-and-technical-data-sheets-library2\)](#)
- [Videos \(/videos\)](#)
- [Literature \(/literature\)](#)
- [Literature Request \(/index.php?ci_id=50636&la_id=1\)](#)
- [White Papers \(/whitepapers\)](#)
- [Application Notes \(/application-notes\)](#)
- [Application Demos \(/index.php?ci_id=141383&la_id=1\)](#)
- [CAD Renderings \(/cad-renderings\)](#)

Contacts


- [Customer Service \(/index.php?ci_id=50608&la_id=1\)](#)
- [Technical Support \(/index.php?ci_id=50609&la_id=1\)](#)
- [Global Sales & Service \(/index.php?ci_id=50610&la_id=1\)](#)

 [\(www.youtube.com/user/SensingAndControl\)](#)

[\(/contact\)](#)
[\(/contact\)](#)

[Terms & Conditions \(/terms & conditions\)](#)

[Privacy Statement \(/index.php?ci_id=2589&la_id=1\)](#)



[\(/contact\)](#)
[itemap\)](#)
[\(/contact\)](#)