


MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929



SWITCH - ENCLOSED

CATALOG LISTING
LSQ081


HARDENED CORROSION RESISTANT
STEEL SHAFT WITH STRAIGHT KNURL



CIRCUIT DIAGRAM



- NOTES
 1 16 GAGE, TYPE SJTO 5 CONDUCTOR CABLE
 2 - SWITCH USES VITON SEALS



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING TORQUE --- 4 IN LBS MAX
 FULL TRAVEL TORQUE --- 4 IN LBS MAX
 PRETRAVEL --- 15° MAX
 DIFFERENTIAL TRAVEL --- 5° MAX
 OVERTRAVEL --- 60° MIN
 TOTAL TRAVEL --- 75° REF

ELECTRICAL DATA

CONTACT ARRANGEMENT

SCALE FULL


DO NOT SCALE PRINT

TOLERANCES
 APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
 REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/64	
ONE PLACE	X,X	0.4/016	X,X
TWO PLACES	X,X,X	0.15/006	X,X,X
THREE PLACES			
ANGLES			

SI METRIC ☐ US CUSTOMARY ☒

DESIGN UNITS



WEIGHT

LSQ081	M	DRAWING NUMBER	ISSUE	4	CHECK	31 JAN 83	CEB	31 JAN 83	CHECK	31 JAN 83	SLB	28 JAN 83	FO-92851-B	DRAWN	REPLACES	PR-11885		
															REVISIONS	A	PR	11885
															B	CO	54082	
															C	CO	79940	
JAK 31 MAR 95																		