



Home > Products > Environmentally Sealed Proximity Sensors > ZS > Product Page

### ZS-00434-01

#### Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback



Actual product appearance may vary.

**One Piece Sensor, Harsh Environment 3-wire dc, Cylindrical, Stainless steel, Ceramic, NO Current Sink, 14 Vdc to 33 Vdc, ZS Series**

#### Features

Hall effect, magnetic field sensitive  
 High frequency sw itching  
 Small housing  
 High level of electronics protection  
 Leadw ire or connector termination  
 Factory mutual certified for Class 1, Division 2, Groups A,B,C,D.

#### Potential Applications

Aircraft landing gear  
 Gun turret position control  
 Door and hatch open/closed monitoring

#### Description

Environment-proof self-contained proximity sensor enclosed in a rugged stainless steel housing, designed to meet the requirements of aerospace, ordnance, marine, mass transit and high performance industrial equipment. Operation by Hall Effect principle, which is used to detect magnetic fields passing in front of the sensing face. Once a target metal is detected, a trigger signal is produced which is then passed through the output conditioning circuitry to give a high or low output, depending on the sensor application.

#### Supporting Documentation

None Available

Product Specifications	
Packaging	One Piece Sensor
Sensor Type	Harsh Environment
Shape	Cylindrical
Dimension	M12
Technology	ECKO
Cable Length	700 mm [28 in]
Operating Frequency	2000 Hz
Load Current	200 mA
Supply Current	10 mA
Housing Material	Stainless Steel
Sensing Face	Ceramic
Gd (mm)	4.31
Guaranteed Actuation Distance	2 mm to 2.99 mm [0.0787 in to 0.1177 in]
Operating Temperature Range	-40 °C to 100 °C [-40 °F to 212 °F]
Shock	100 g 6 ms
Vibration	*
Supply Voltage	14 Vdc to 33 Vdc
BITE Yes/No	No
Short Circuit Yes/No	Yes
Pressure proof Yes/No	No
Reverse polarity Yes/No	Yes
MTBF (hrs)	144000
Conducted suscept	Mil-STD-461B
Conducted emission	Mil-STD-461B
RF suscept	Mil-STD-461B
RF emission	Mil-STD-461B
LEMP	DEF 07-55, T2, S5
Insulation Resistance	50 Mohm @ 500 Vdc
Comments	*Freq range 10 to 500Hz, Cross Over Freq (COF) 58-62Hz, 0.75ms-2 below COF 100ms-2 above COF
Termination	Leadwire,Connector
Connector Type	M83723-72R-1005N
Output Type	Normally Open, Current Sinking
Series Name	ZS

#### My Links

[Login to iCOM](#)  
[Login as Rep/AD](#)  
[Login as Guest](#)  
[Login to Digital University](#)

#### Keyword Search

Search for product and support information.

All Sensing and Control ▾

#### Product Search

Part number search:

Use (\*) to expand search

#### Specification Search