

NE8FAV-C5-DAE

New: With ESD protective push tab improving electrostatic discharge and component protection. Furthermore, the asymmetric design offers more space for labeling purposes.

Vertical PCB mount RJ45 receptacle, CAT5e, A-Series cutout with latch lock, max. panel thickness 3 mm

The etherCON Series is a ruggedized and lockable RJ45 connector system, optimized for pro audio, video and lightning network applications. The chassis connectors are shaped to fit into standardized panels out of the entertainment industry.

The all plastic A-Series offers the most space saving and cost effective design.

Attention! Does not intermate with CAT6 cable connector NE8MC6-MO and NKE6S* cables.



Features & Benefits

- New ESD push tab material for improved electrostatic discharge and component protection
- Asymmetric tab design offers more space for labeling
- Most space saving and cost effective design
- PoE+ compliant according to 802.3at Type2
- Vertical PCB design at 24 mm distance to front panel – fits the widely accepted industry standard dimension for XLRs, 1/4" jacks etc.
- Approved latch lock system
- Accommodates rugged etherCON NE8MX* or any standard RJ45 plug
- Isolated to panel ground
- CAT5e performance according to ISO/IEC 11801 and TIA/EIA 568-C.2
- Compound material of push tab improves ESD protection

Technische Informationen

Produkte	
Title	NE8FAV-C5-DAE
Type	Chassis
Connection Type	etherCON
Gender	Female

Elektrisch	
Contact resistance	< 50 m Ω
Dielectric strength	1 kV DC
Frequency range	1 – 100 MHz
Insulation resistance	> 0.5 G Ω
Rated current per contact	1.5 A
Rated voltage	< 50 V
Transmission performance	CAT 5e, acc. TIA/EIA 586C.2, IEC11801
Power over Ethernet	PoE+ acc. to IEEE 802.3at

Mechanische Daten	
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Panel thickness	Max. 3 mm (0.12")
Wiring	Vertical PCB mount
Locking device	Rear mounting
Chassis shape	A
Mounting	A-Screw

Material	
Contact plating	0.2 µm Au over Ni plating
Contacts	Bronze (CuSn8)
Locking element	HPPA
Shell	PBT D202G30

Umwelt	
Flammability	UL 94 V-0
Temperature range	-30 °C to +80 °C
Solderability	Complies with IEC 68-2-20