



+ RELAYS, CONTACTORS & SWITCHES

POWER RELAYS



✓ Active

TE CONNECTIVITY (TE)

MDR-67-3=MDR

Potter & Brumfield | MDR Rotary Relay

MDR-67-3

TE Internal Number: 9-1393139-3

Not EU RoHS Compliant

Not EU ELV Compliant

Power Relay Type Rotary

Coil Magnetic System Latching

Coil Resistance (Ω) 36

Contact Arrangement 4 Form C, 4PDT, 4 C/O

DOCUMENTATION

Catalog Pages/Data Sheets

5-1773450-5_sec12_MDR

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Power Relay Type Rotary

Electrical Characteristics

Coil Current (A) .778
Coil Magnetic System Latching
Coil Resistance (Ω) 36
Actuating System DC
Input Voltage (VDC) 28
Insulation Initial Dielectric Between Contacts & Coil (V) 1308
Coil Power Rating (W) 21.8

Contact Features

Contact Arrangement 4 Form C, 4PDT, 4 C/O

Dimensions

Height 79.5 mm [3.13 in]
Base Dimensions 66.68 x 66.68 mm [2.625 x 2.625 in]

Usage Conditions

Operating Temperature Range ($^{\circ}\text{C}$) 0 – 65

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
