

## MDR-136-1 Product Details



### MDR-136-1

TE Part Number: 1393139-9

✓ Active

[Add to Part List](#)

### Rotary Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Contact Arrangement = 8 Form C, 8PDT, 8 C/O
- DC Actuating System
- Input Voltage = 28 VDC
- Coil Current = .362 Amps.
- Coil Resistance = 76 Ω

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Dimensional Drawing](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Comment = Small

#### Electrical Characteristics:

- Actuating System = DC
- Input Voltage (VDC) = 28
- Coil Current (Amps.) = 0.362
- Coil Resistance (Ω) = 76
- Coil Power, Nominal (W) = 10.00
- Breakdown Volts RMS (V) = 1308

#### Termination Related Features:

- Base Dimensions (mm [in]) = 66.68 x 66.68 [2.625 x 2.625]
- Height (mm [in]) = 89.70 [3.530]

#### Configuration Related Features:

- [Contact Arrangement](#) = 8 Form C, 8PDT, 8 C/O
- Coil Magnetic System = Non-Latching

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

#### Conditions for Usage:

- Temperature Range (°C) = 0 - 65

#### Other:

- Brand = Potter & Brumfield