

## Blind sleeve - CES-LTPG-GY - 0801716

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Large blind sleeve, material: SEBS



### Product Description

Blind sleeves seal feed-through sections that are not required in CES sealing frames



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	31.2 g
Custom tariff number	85472000
Country of origin	Poland

### Technical data

#### Dimensions

Conductor sealing range	Blind sleeve
Length	29.5 mm
Width	19.5 mm
Height	17 mm

#### Ambient conditions

Degree of protection	IP54 (for sealing frames with screw locking. IP44 sealing frames with locking latch.)
Ambient temperature (operation)	-40 °C ... 80 °C (static)

#### General

Product description	Blind sleeves seal feed-through sections that are not required in CES sealing frames
No. of conductors	0
Material	SEBS

# Blind sleeve - CES-LTPG-GY - 0801716

## Technical data

### General

Flammability rating according to UL 94	V0
Color	gray

### Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

## Classifications

### eCl@ss

eCl@ss 4.0	27081002
eCl@ss 4.1	27081002
eCl@ss 5.0	27081002
eCl@ss 5.1	27081002
eCl@ss 6.0	27081002
eCl@ss 7.0	27081002
eCl@ss 8.0	27069220

### ETIM

ETIM 3.0	EC000879
ETIM 4.0	EC000451
ETIM 5.0	EC000451

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

## Approvals

### Approvals

---

### Approvals

UL Recognized / cUL Recognized / GL / cULus Recognized

---

# Blind sleeve - CES-LTPG-GY - 0801716

## Approvals

Ex Approvals

---

Approvals submitted

## Approval details

UL Recognized


cUL Recognized

GL

cULus Recognized

## Drawings

Dimensional drawing



Dimensional drawing