

## Shrink sleeve - WMS 6,4 (60X10)RXL YE - 0803104

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Shrink sleeve, Roll, yellow, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, perforated, Lettering field: 60 x 10 mm



The illustration shows WMS 6,4 (30X10)R

### Why buy this product

- WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- The sleeves are pre-assembled for optimum use of material
- The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- The sleeves remain flexible after shrinking
- Up to four markers per sleeve are separated by perforations
- UL 224 (125°C, 600 V, all tubing)
- CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)

### Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	1,100.000 g
Custom tariff number	39173200
Country of origin	China

### Technical data

#### Dimensions

Length (b)	60 mm
Width (a)	10 mm
Cable diameter	6.4 mm

#### General

Color	yellow
Base element material	polyolefine
Components	Halogen-free
Material	Polyolefine

## Shrink sleeve - WMS 6,4 (60X10)RXL YE - 0803104

### Technical data

#### General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2500

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------