

DIM MULTieco | Control units for light management systems



Areas of application

- Ceiling or independent installation via ECO CI KIT possible

Product benefits

- Complies with MINERGIE and EU Ecodesign requirements
- Energy savings up to 75 % (compared to CCG + T8 lamp without sensors)

Product features

- 1 channel 1...10 V control unit
- Suitable for daylight-dependent control with presence function
- Maximum power consumption in stand-by mode: 0.5 W
- Integrated load contact
- 14 operating modes via DIP switches for daylight- or presence-dependent switching
- Up to 3 controllers can be synchronized for a central presence function
- Manual dimming and setpoint setting via standard switches


Product datasheet

Technical data

Electrical data

Nominal voltage	100...240 V
Mains frequency	50...60 Hz
System wattage	0.90 W

Dimensions & weight



Length	118.0 mm
Width	30.0 mm
Height	21.0 mm
Product weight	50.00 g

Temperatures

Ambient temperature range	0...+50 °C
---------------------------	------------

Capabilities

Dimming interface	1...10 V
Number of control outputs	1
Load contact	5 A
Type of installation	Luminaire integration/Ceiling integration

Certificates & standards






Type of protection	IP20
--------------------	------

Equipment / Accessories

- Suitable for up to 2 sensors (compatible with all MULTI 3 sensors)
- Suitable for up to 10 electronic control gears with 1...10 V dimming interface

Product datasheet

Download Data

File	
	Brochures Energy saving
	Declarations of conformity Declaration of conformity MULTleco ECO CI Kit
	Installation/Operation notice DIM MULTleco control unit for 1...10 V signal
	Installation guide ECO CI Kit mounting kit
	Installation guide DIM MULTleco control unit for 1...10 V signal

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321507273		Shipping carton box 25	218 mm x 170 mm x 170 mm	6.30 dm ³	2236.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.