



## 1461352-5 Product Details

[Share](#) | [Print](#) | [Email](#)


1461352-5

TE Internal Number: 1461352-5

 [Active](#)

### Industrial Relays (General Purpose)

 [Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Relay Type = Miniature Power PCB Relay
- Relay Style = PCB
- PCH Series
- Contact Arrangement = 1 Form A, SPST-NO
- Contact - Rated Current = 5 A

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [PCH-L2M CUSTOMER DRAWING](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- [PCH Series Relay Data Sheet - English](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Series](#) = PCH
- [Termination Type](#) = Through Hole

#### Electrical Characteristics:

- [Contact - Rated Current \(A\)](#) = 5
- [Coil Resistance \(Ω\)](#) = 720
- [Coil - Rated Power \(mW\)](#) = 200
- [Actuating System](#) = DC
- [Input Voltage \(VDC\)](#) = 12
- Insulation - Special Features = None

#### Contact Features:

- Relay Type = Miniature Power PCB Relay
- [Mounting Options](#) = PC Board
- [Enclosure Type](#) = Flux-Tight
- [Contact Base Material](#) = Silver Tin Oxide
- Approx. Dimensions (L x W x H) (mm [in]) = 20.00 x 10.00 x 15.20 [.788 x .394 x .598]

#### Configuration Features:

- Relay Style = PCB
- [Contact Arrangement](#) = 1 Form A, SPST-NO
- [Coil - Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- Status Indicator = None

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive
- Approved Standards = UL Recognized, CSA Certified, TUV Approved, VDE Component Mark

#### Other:

- Brand = OEG

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

[>](#)

