

Marker for terminal blocks - UCT1U-TM 5 - 0803204

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

UniCard materials for thermal transfer printers, for marking terminal blocks from Weidmüller, Conta Clip, and Klemmsan, 72-section, offset foot, can be marked with THERMOMARK CARD and BLUEMARK, color: white



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
GTIN	 4 055626 010991
GTIN	4055626010991
Weight per Piece (excluding packing)	14.000 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	10 mm
Width (a)	5 mm
Unit of measurement	6 m

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Note	Can be labeled via thermal transfer
Color	white
Components	free from silicone, halogen, and cadmium

Marker for terminal blocks - UCT1U-TM 5 - 0803204

Technical data

General

Flammability rating according to UL 94	V0
Material	PC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	72
Number of individual labels per row	12
RoHS compliant	Yes
Printability	Thermal transfer
	UV LED technology
	Direct laser marking
Device	5146464 THERMOMARK CARD
	5147888 BLUEMARK LED
	5147999 BLUEMARK CLED
	0831831 TOPMARK LASER
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	clip on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0