

Conductor marking collar - UCT-WMS 4,7 (12X5,5) BU - 0830212

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking collar, Sheet, blue, unlabeled, can be labeled with: THERMOMARK CARD, BLUEMARK CLED, BLUEMARK LED, TOPMARK LASER, Mounting type: slide on, for terminal block width: 5.2 mm, Cable diameter: 2.5-4.7 mm, Lettering field: 12 x 5.5 mm

Product Features

- The UCT-WMS ... UniCard labeling range includes markers that can be threaded onto conductors
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the THERMOMARK CARD and the BLUEMARK LED
- The markers support multi-line labeling
- The format automatically ensures printing with a high degree of positioning accuracy
- The sheets provide space for including function texts

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	6 pc
Weight per Piece (excluding packing)	16.67 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	12 mm
Width (a)	5.5 mm
Height	7.1 mm
Cable diameter	2.5 mm ... 4.7 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Note	Can be labeled via thermal transfer
Color	blue
Components	free from silicone and halogen

Conductor marking collar - UCT-WMS 4,7 (12X5,5) BU - 0830212

Technical data

General

Flammability rating according to UL 94	V0
Material	PC V0
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	45
Number of individual labels per row	9
RoHS compliant	Yes
Printability	Thermal transfer Inkjet printing
Device	5146464 THERMOMARK CARD 5147888 BLUEMARK LED 5147999 BLUEMARK CLED
Ink ribbon	5146613 THERMOMARK CARD-UCT-MAG3 0801371 THERMOMARK-RIBBON 110-TC 5147421 BLUEMARK FLUID-CARTRIDGE 5146662 BLUEMARK CLED-FLUID-CARTR.
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	slide on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Conductor marking collar - UCT-WMS 4,7 (12X5,5) BU - 0830212

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410