

Cable marker carrier - WM-CARRIER/B (48X10)LPR - 0830423


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker carrier, transparent, unlabeled, mounting type: Assembly with cable binders, cable diameter: ≥ 6 mm, lettering field size: 48 x 10 mm



RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
GTIN	 4 046356 716130
GTIN	4046356716130
Weight per Piece (excluding packing)	0.800 g
Custom tariff number	39204910
Country of origin	Denmark

Technical data

Dimensions

Length (b)	70 mm
Width (a)	14 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (assembly)	10 °C

General

Color	transparent
Type	Mounting set
Components	halogen-free

Cable marker carrier - WM-CARRIER/B (48X10)LPR - 0830423

Technical data

General

Material	PVC/polyester
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Adhesive	Acrylic
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Marking mounting type	Assembly with cable binders

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC002248
ETIM 6.0	EC001530

Cable marker carrier - WM-CARRIER/B (48X10)LPR - 0830423

Classifications

ETIM

ETIM 7.0	EC001530
----------	----------

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Device marking

Label - EML (40X6)R - 0830481



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, lettering field size: 40 x 6 mm, Number of individual labels: 2500

Label - EML (40X6)R YE - 0830482



Label, Roll, yellow, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, lettering field size: 40 x 6 mm, Number of individual labels: 2500

Labeled device marker

Cable marker carrier - WM-CARRIER/B (48X10)LPR - 0830423

Accessories

Label - EML (40X6)R CUS - 0830487



Label, can be ordered: by line, white, labeled according to customer specifications, mounting type: adhesive, lettering field size: 40 x 6 mm, Number of individual labels: 2500

Label - EML (40X6)R YE CUS - 0830488



Label, can be ordered: by line, yellow, labeled according to customer specifications, mounting type: adhesive, lettering field size: 40 x 6 mm, Number of individual labels: 2500
