

Marker for terminal blocks - UC-TM 8 YE - 0818386

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for terminal blocks, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 8.2 mm, Lettering field: 7.6 x 10.5 mm

Product Features

- The UC-TM ... UniCard labeling range includes markers for products with tall marker grooves
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- The markers support multi-line labeling
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	14.0 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Width (a)	8 mm
-----------	------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Note	Can be labeled with CMS
Color	yellow
Components	free from silicone and halogen
Flammability rating according to UL 94	V2

Marker for terminal blocks - UC-TM 8 YE - 0818386

Technical data

General

Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	56
Number of individual labels per row	7
Marking mounting type	Snap into tall marker groove

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410