

Sensor/Actuator cable - SAC-5P-M12MS/ 0,6-927/M12FS VA - 1402945

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

5-pos. cable, black PVC, shielded, shielded plug, straight M12, A-coded, on shielded socket, straight M12, A-coded with VA knurl, length: 0.6 m

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	50 STK
Weight per Piece (excluding packing)	180.000 g
Custom tariff number	85444290
Country of origin	Poland

Technical data

General

Number of positions	5
---------------------	---

Cable

Cable type	DeviceNet™
Cable type (abbreviation)	927
UL AWM style	2464 (80°C/300 V)
Conductor cross section	2x 0.34 mm ² (Signal line)
	2x 0.34 mm ² (Power supply)
	1x 0.38 mm ² (Drain wire)
AWG signal line	22
AWG power supply	22
Conductor structure signal line	44x 0.10 mm
Conductor structure, voltage supply	44x 0.10 mm
Core diameter including insulation	2.55 mm (Signal line)
	1.37 mm (Power supply)
Thickness, insulation	≥ 0.3 mm (Wire insulation power supply)
Wire colors	Red-black, blue-white
Twisted pairs	2 cores to the pair
Type of pair shielding	Aluminum-lined polyester foil
Overall twist	2 pairs with filler elements, around a drain wire in the center to the core
Shielding	Tinned copper braided shield
Optical shield covering	85 %
External sheath, color	black

Sensor/Actuator cable - SAC-5P-M12MS/ 0,6-927/M12FS VA - 1402945

Technical data

Cable

Outer sheath thickness	≥ 1 mm
External cable diameter D	8.3 mm $\pm 0,3$ mm
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Cable weight	83 kg/km
Outer sheath, material	PVC
Material conductor insulation	Foamed PP (Signal line)
	PVC (Power supply)
Conductor material	Tin-plated Cu litz wires
Insulation resistance	≥ 20 M Ω *km
Conductor resistance	≤ 56 Ω /km
Working capacitance	approx. 39.8 nF (Signal line, Core-Core)
	≤ 4000 pF (Signal line, Core-Shield)
Wave impedance	120 Ω ± 12 Ω (f = 1 MHz)
Signal runtime	4.46 ns/m
Nominal voltage, cable	≤ 300 V
Test voltage, cable	2000 V (50 Hz, 1 min.)
Flame resistance	In acc. with UL 1581, section 1061
Ambient temperature (operation)	-30 °C ... 80 °C

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values