

## Conductor marker carrier - PATO 1/12 - 0827081

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Conductor marker carrier, transparent, unlabeled, mounting type: clip on, cable diameter range: 2 ... 3.5 mm, lettering field size: 4 x 12 mm

### Your advantages

- Can be labeled using UC-WMT ... and US-WMT ... plastic labels or EMT insert strips
- These marking collars are used for subsequent labeling of systems that have already been wired



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	1000 pc
GTIN	 4 046356 416733
GTIN	4046356416733
Weight per Piece (excluding packing)	0.340 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	12 mm
Width (a)	5.6 mm
Cable diameter	2 mm ... 3.5 mm

#### Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
---------------------------------	------------------

# Conductor marker carrier - PATO 1/12 - 0827081

## Technical data

### General

Color	transparent
Type	Profile
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC
Marking mounting type	clip on

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

## Classifications

### eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC002248
ETIM 6.0	EC001530
ETIM 7.0	EC001530

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410

## Conductor marker carrier - PATO 1/12 - 0827081

### Classifications

#### UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504