

Conductor marker carrier - PATG 0/23 - 0828046

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 0.6 ... 1.2 mm, lettering field size: 23 x 4 mm

Your advantages

- The corresponding UC-WMT ..., US-WMT ..., UCT-WMT ... and EMT ... insert labels are used for marking

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| Minimum order quantity | 1000 pc |
| GTIN |  4 046356 467018 |
| GTIN | 4046356467018 |
| Weight per Piece (excluding packing) | 0.280 g |
| Custom tariff number | 39269097 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|----------------|-------------------|
| Length (b) | 23 mm |
| Width (a) | 5 mm |
| Cable diameter | 0.6 mm ... 1.2 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -50 °C ... 80 °C |
|---------------------------------|------------------|

General

| | |
|-------|-------------|
| Color | transparent |
|-------|-------------|

Conductor marker carrier - PATG 0/23 - 0828046

Technical data

General

| | |
|---|----------------------|
| Type | Profile |
| Components | Silicone-free |
| Flammability rating according to UL 94 | V0 |
| Material | PVC |
| RoHS compliant | Yes |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Marking mounting type | slide-on |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |
|------------|---|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27061700 |
| eCl@ss 4.1 | 27061700 |
| eCl@ss 5.0 | 27400400 |
| eCl@ss 5.1 | 27400400 |
| eCl@ss 6.0 | 27149100 |
| eCl@ss 7.0 | 27149153 |
| eCl@ss 8.0 | 27400401 |
| eCl@ss 9.0 | 27400401 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC002248 |
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |

Conductor marker carrier - PATG 0/23 - 0828046

Classifications

UNSPSC

| | |
|--------------|----------|
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131504 |
| UNSPSC 18.0 | 39131504 |
| UNSPSC 19.0 | 39131504 |
| UNSPSC 20.0 | 39131504 |
| UNSPSC 21.0 | 39131504 |