

Cable marker - UC-WMTB (44X15) - 0828376

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Assembly with cable binders, Cable diameter: >7 mm, Lettering field: 44 x 15 mm



Product Features

- The UC-WMTB ... UniCard labeling range includes markers that can be secured using standard cable binders
- For large-surface labeling of conductors and cables > 7 mm in diameter
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The format automatically ensures printing with a high degree of positioning accuracy
- The sheets provide space for including function texts

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	10.0 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Width (a)	44 mm
-----------	-------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Cable marker - UC-WMTB (44X15) - 0828376

Technical data

General

Number of individual labels	4
Number of individual labels per row	1
Min. cross section	16 mm ²
Printability	Inkjet printing
	Plotter
Device	5147888 BLUEMARK LED
	5147999 BLUEMARK CLED
	5144615 CMS-P1-PLOTTER
	5146121 P1 UC-MAG 6
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	Assembly with cable binders

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401

Cable marker - UC-WMTB (44X15) - 0828376

Classifications

eCl@ss

eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410