

## Cable marker - UC-WMTB (44X15) BU - 0828381

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marker, Sheet, blue, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Assembly with cable binders, Cable diameter: >7 mm, Lettering field: 44 x 15 mm

### Product Features

- The UC-WMTB ... UniCard labeling range includes markers that can be secured using standard cable binders
- For large-surface labeling of conductors and cables > 7 mm in diameter
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The format automatically ensures printing with a high degree of positioning accuracy
- The sheets provide space for including function texts

### Key Commercial Data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 pc     |
| Minimum order quantity               | 10 pc    |
| Weight per Piece (excluding packing) | 10.0 g   |
| Custom tariff number                 | 39269097 |
| Country of origin                    | Germany  |

### Technical data

#### Dimensions

|           |       |
|-----------|-------|
| Width (a) | 44 mm |
|-----------|-------|

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

#### General

|  |                                |
|--|--------------------------------|
| Color                                  | blue                           |
| Components                             | free from silicone and halogen |
| Flammability rating according to UL 94 | V2                             |
| Material                               | PA                             |
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1)    |

## Cable marker - UC-WMTB (44X15) BU - 0828381

### Technical data

#### General

|  |                                     |
|--|-------------------------------------|
| Number of individual labels  | 4                                   |
| Number of individual labels per row                                      | 1                                   |
| Min. cross section   | 16 mm <sup>2</sup>                  |
| Printability   | Inkjet printing                     |
|  | Plotter                             |
| Device   | 5147888 BLUEMARK LED                |
|  | 5147999 BLUEMARK CLED               |
|  | 5144615 CMS-P1-PLOTTER              |
|  | 5146121 P1 UC-MAG 6                 |
| Test for substances that would hinder coating with paint or varnish      | VW PV 3.10.7:2005-02                |
| Result   | Test passed                         |
| Test specification weathering-resistance                                 | Following ISO 4892-2:2013-03        |
| Test duration  | 96 h                                |
| Wipe resistance test result  | Test passed                         |
| Salt spray test specification  | DIN EN ISO 9227:2012-09             |
| Test duration  | 96 h                                |
| Salt spray testing result  | Test passed                         |
| Alternating condensation climate with SO <sub>2</sub> test specification | DIN 50018:2013-05                   |
| Climate level  | AHT 1.0 S                           |
| Cycles   | 2                                   |
| Condensation test result   | Test passed                         |
| Wipe resistance of test specification inscriptions                       | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result   | Test passed                         |
| Marking mounting type  | Assembly with cable binders         |

#### Standards and Regulations

|  |                             |
|--|-----------------------------|
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V2                          |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27400401 |
| eCl@ss 7.0 | 27400401 |

## Cable marker - UC-WMTB (44X15) BU - 0828381

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 8.0 | 27400401 |
| eCl@ss 9.0 | 27400401 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001530 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |