

Conductor marking - UCT-WMCO 4,1 (12X4) YE - 0831208

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Conductor marking, Sheet, yellow, unlabeled, can be labeled with: THERMOMARK PRIME, THERMOMARK CARD, BLUEMARK CLED, BLUEMARK LED, TOPMARK LASER, Mounting type: clip on, Cable diameter: 3.5-4.1 mm, Lettering field: 12 x 4 mm



Why buy this product

- The UCT-WMCO ... UniCard labeling range includes markers for the subsequent labeling of conductors by simply snapping on
- Large-surface labeling option in a space-saving design
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- Secure tight fit even in the event of vibrations
- The format automatically ensures printing with a high degree of positioning accuracy



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	6 STK
GTIN	 4 055626 006482
GTIN	4055626006482
Weight per Piece (excluding packing)	13.330 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	12 mm
Width (a)	4 mm
Cable diameter	3.5 mm ... 4.1 mm

Ambient conditions

Conductor marking - UCT-WMCO 4,1 (12X4) YE - 0831208

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	yellow
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V0
Material	PC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	32
Number of individual labels per row	8
RoHS compliant	Yes
Printability	Thermal transfer
	UV LED technology
Device	5146464 THERMOMARK CARD
	5147888 BLUEMARK LED
	5147999 BLUEMARK CLED
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	clip on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0