

Conductor marking collar - LBHZ 2/WH:UNBEDRUCKT - 1013575


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking collar, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 1.5 ... 3.2 mm, lettering field size: 4.5 x 10 mm, Number of individual labels: 10



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
GTIN	 4 017918 013851
GTIN	4017918013851
Weight per Piece (excluding packing)	1.060 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	10 mm
Width (a)	4.5 mm
Height (c)	6 mm
Cable diameter	1.5 mm ... 3.2 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Note	Can be labeled with CMS
Color	white

Conductor marking collar - LBHZ 2/WH:UNBEDRUCKT - 1013575

Technical data

General

Type	Card form
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	10
Number of individual labels per row	10
Marking mounting type	slide-on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410

Conductor marking collar - LBHZ 2/WH:UNBEDRUCKT - 1013575

Classifications

UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504