

Conductor marker carrier - PATG 2/10 - 1013818

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Conductor marker carrier, transparent, unlabeled, Mounting type: slide on, Cable diameter: 2-4 mm, Lettering field: 4 x 10 mm

The figure shows version

Product Features

- The corresponding UC-WMT ..., US-WMT ..., and EMT insert labels are used for marking
- These conductor marking systems consist of marker carriers and insert labels
- The PATG ... collar is a captive marker carrier
- Can be used to mark conductors with a diameter of 0.6 ... 50 mm

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| Minimum order quantity | 1000 pc |
| GTIN |  4 017918 014001 |
| Weight per Piece (excluding packing) | 0.28 g |
| Custom tariff number | 39269097 |
| Country of origin | Germany |

Technical data

Environmental Product Compliance

| | |
|------------|-----------------|
| REACH SVHC | DOTE 15571-58-1 |
|------------|-----------------|

Dimensions

| | |
|----------------|---------------|
| Width (a) | 10 mm |
| Cable diameter | 2 mm ... 4 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -50 °C ... 80 °C |
|---------------------------------|------------------|

General

Conductor marker carrier - PATG 2/10 - 1013818

Technical data

General

| | |
|---|----------------------|
| Color | transparent |
| Components | Silicone-free |
| Flammability rating according to UL 94 | V0 |
| Material | PVC |
| RoHS compliant | Yes |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Marking mounting type | slide on |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27400401 |
| eCl@ss 9.0 | 27400401 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001530 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

