

## Cable gland - G-EDSWU-M20-M66L-STES-S - 1411091

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, cable gland material: Stainless steel 316L, application: Ex, external cable diameter 12.5 mm ... 20.9 mm, shielding: yes, connecting thread: M20 x 1.5, color: silver

### Product Description

Cable gland, for armored cables (SWA / AWA / PWA / STA / SWB / ASA / CY / SY)


### Your advantages

- If space is restricted at the fixing location of the screw connection, the armor can be attached at a location where there is more room to move. Final assembly can then be easily completed in the restricted space conditions at the fixing location of the screw connection.
- Armor connected via PE cone
- Weatherproof sealing material

RoHS



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 922043
GTIN	4046356922043
Weight per Piece (excluding packing)	250.000 g
Custom tariff number	73269098
Country of origin	United Kingdom

### Technical data

#### Dimensions

Length	75 mm
Thread pitch	1.5 mm
Wrench size, union nut	30.5 mm

# Cable gland - G-EDSWU-M20-M66L-STES-S - 1411091

## Technical data

### Dimensions

Wrench size, support	30.5 mm
Hexagon angular dimension	33.6 mm
Length of the connecting thread	15 mm
External cable diameter	12.5 mm ... 20.9 mm
Cable diameter without cable sheath	6.5 mm ... 14 mm
Armor connection method	Cone
Armor thickness	0.8 mm ... 1.25 mm (Stepped cone side (SWA/...))
	0 mm ... 0.8 mm (Grooved cone side (STA/...))
Cable diameter without armor	6.5 mm ... 14 mm (Filler beneath the armor)
Cable types that can be used	Depending on the material of the housing wall (SWA/AWA/PWA/STA/ASA/CY/SY/SWB)

### Ambient conditions

Degree of protection (IP)	IP66 (using the corresponding A-SEW-...P-W flat gasket)
	IP67 (using the corresponding A-SEW-...P-W flat gasket)
	IP68 (using the corresponding A-SEW-...P-W flat gasket)
Ambient temperature (operation)	-60 °C ... 130 °C (static)

### General

Note	with seal for conductor outer and inner jacket
Cable gland material	Stainless steel 316L
Seal material	EPDM
Cable seal material	EPDM
Thread type connection side	M20 x 1.5
Color	silver
Impact energy	20.00 J
Assembly instructions	With integrated grounding cones, sealed to IP66/IP67/IP68 thanks to the use of the A-SEW-20-P-W flat gasket (item 1411283)
Connection	If space is restricted at the fixing location of the screw connection, the armor can be attached at a location where there is more room to move. Final assembly can then be easily completed in the restricted space conditions at the fixing location of the screw connection.
Standards/specifications	EN 60079-0, -1, -7, -15, -31
	IEC 60079-0, -1, -7, -15, -31
	EN 50262
	IEC 62444
	IEC 61241-0:2004
Manufacturer	CMP
Manufacturer product number	20T3CDS1RA4
Manufacturer Designation	20 TRITON CDS S. STEEL GLAND

# Cable gland - G-EDSWU-M20-M66L-STES-S - 1411091

## Technical data

### General

Suited for EX-applications	yes
----------------------------	-----

### Standards and Regulations

Standards/regulations	EN 60079-0, -1, -7, -15, -31
	IEC 60079-0, -1, -7, -15, -31
	EN 50262
	IEC 62444
	IEC 61241-0:2004
ATEX	Sira 13ATEX1073X
	Sira 13ATEX4079X
	Ex II 2G, II 1D, Ex d IIC Gb, Ex e IIC Gb, Ex ta IIIC Da, Ex II 3G Ex nR IIC Gc, Ex I M2, Ex d I Mb, Ex e I Mb
IECEX	IECEX SIR 13.0028X
	Ex d IIC Gb, Ex e IIC Gb, Ex nR IIC Gc, Ex ta IIIC Da, Ex d I Mb, Ex e I Mb


### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

# Cable gland - G-EDSWU-M20-M66L-STES-S - 1411091

Dimensional drawing



Dimensional drawing

## Classifications

### eCl@ss

eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27149100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

### ETIM

ETIM 4.0	EC000441
ETIM 5.0	EC000441
ETIM 6.0	EC000441
ETIM 7.0	EC000441

### UNSPSC

UNSPSC 13.2	39121311
UNSPSC 18.0	39121311

# Cable gland - G-EDSWU-M20-M66L-STES-S - 1411091

## Classifications

### UNSPSC

UNSPSC 19.0	39121311
UNSPSC 20.0	39121311
UNSPSC 21.0	39121311

## Approvals

### Approvals

---

Approvals

UL Listed

---

Ex Approvals

IECEX / ATEX / CSA / CSAus / EAC Ex / cCSAus

---

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.html">database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.html</a>	E200163
-----------	--	--	---------

## Accessories

### Accessories

#### Flat nut

Counter nut - A-INL-M20-S-S - 1411249



Counter nut, material: Stainless steel 1.4305, for threads M20 x 1.5, color: silver

---

### Seal

## Cable gland - G-EDSWU-M20-M66L-STES-S - 1411091

### Accessories

Flat gasket - A-SEW-20-P-W - 1411283

Flat gasket, material: Nylon, for threads M20, color: white

