

Protective covers - HC-B 6-TMS-SD-IP66 - 1411494

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




HEAVYCON ADVANCE, IP66, B6 protective cover for panel mounting side, with screw locking, with retaining cord, diameter of retaining cord eyelet: 3 mm



COMPLETE

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 918688
GTIN	4046356918688
Weight per Piece (excluding packing)	48.000 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	39.3 mm
Width	55 mm
Length	89.5 mm

Ambient conditions

Degree of protection (IP)	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

General

Size	B6
Type	HC-ADVANCE protective cover

Protective covers - HC-B 6-TMS-SD-IP66 - 1411494

Technical data

General

Housing type	Protective cover
Color	gray
Locking type	Screw locking
Torque	3 Nm (Locking screw)
Material	PA
Seal material	NBR
Material lock	Stainless steel
Material of locking screw	Stainless steel
Material, protective cover	PA
Flammability rating according to UL 94	V0
Assembly instructions	Tightening torque of locking screw: 3 Nm

Standards and Regulations


Flammability rating according to UL 94	V0
----------------------------------------	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100

Protective covers - HC-B 6-TMS-SD-IP66 - 1411494

Classifications

eCl@ss

eCl@ss 5.1	27149100
eCl@ss 6.0	27261200
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002314
ETIM 5.0	EC002314
ETIM 6.0	EC002314
ETIM 7.0	EC002314

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	--	--------------------------

