

Housing - HC-STA-B06-HHFS-1TTM32-EL-AL - 1412567

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Sleeve housing B6, for single locking latch, Material: Die-cast aluminum, salt water resistant, Cable outlets: 1, straight, Height: 72 mm, Cable gland: none, Gland: no, 1x M32, Standard

Why buy this product

- good shielding in the event of electromagnetic interference



Key Commercial Data

| | |
|----------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 STK |
| GTIN |  4 055626 059075 |
| GTIN | 4055626059075 |
| Custom tariff number | 85389099 |
| Country of origin | China |

Technical data

Dimensions

| | |
|--------|-------|
| Height | 72 mm |
| Width | 44 mm |
| Length | 60 mm |

Ambient conditions

| | |
|----------------------------------------|-------------|
| Degree of protection of housing (IP) | IP66 |
| | IP67 |
| Degree of protection of housing (NEMA) | 4 (UL 50e) |
| | 4X (UL 50e) |

Housing - HC-STA-B06-HHFS-1TTM32-EL-AL - 1412567

Technical data

Ambient conditions

| | |
|---------------------------------|-------------------|
| | 12 (UL 50e) |
| Ambient temperature (operation) | -40 °C ... 125 °C |

General

| | |
|------------------------------|-------------------------------------------------------------------------------------|
| Note | For contact inserts HC-B6, BB10, DD24, M Tall housings for extra large wiring space |
| Size | B6 |
| Housing type | Sleeve housing |
| Color | silver |
| Locking type | for single locking latch |
| No. of cable outlets | 1 |
| Cable exit | straight |
| Screw connection | none |
| Type of the screw connection | 1x M32 |
| Housing material | Die-cast aluminum, salt water resistant |
| Housing surface material | Uncoated |

Environmental Product Compliance

| | |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Approvals

Approvals

Approvals

EAC / GL / UL Recognized / cUL Recognized / cULus Recognized





Ex Approvals

Approval details

| | | |
|-----|-------------------------------------------------------------------------------------|---------------------|
| EAC |  | 7500651.22.01.00246 |
|-----|-------------------------------------------------------------------------------------|---------------------|

Housing - HC-STA-B06-HHFS-1TTM32-EL-AL - 1412567

Approvals

| | | | |
|------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|------------|
| GL |  | http://exchange.dnv.com/tari/ | 6196614 HH |
| UL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | E255026 |
| cUL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | E255026 |
| cULus Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | |