

Housing - HC-ADV-B16-HLWH-1TTM25-MF-BK - 1420921


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing B16, Screw locking, Material: Die-cast aluminum, salt water resistant, Cable outlets: 1, straight, Height: 74 mm, Cable gland: none, Gland: no, 1x M25, Increased environmental requirements

RoHS

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 STK |
| GTIN |  4 055626 249209 |
| GTIN | 4055626249209 |
| Weight per Piece (excluding packing) | 280.000 g |
| Custom tariff number | 85389099 |
| Country of origin | China |

Technical data

Dimensions

| | |
|-------------------------------|----------|
| Height | 74 mm |
| Width | 57 mm |
| Length | 125.5 mm |
| Length of the assembly cutout | 86 mm |
| Width of the assembly cutout | 35 mm |

Ambient conditions

| | |
|--|---------------------------|
| Degree of protection of housing (IP) | IP66 |
| | IP68 (0.2 bar/24 h) |
| | IP69K (ISO 20653:2013-02) |
| Degree of protection of housing (NEMA) | 4 (UL 50e) |
| | 4X (UL 50e) |

Housing - HC-ADV-B16-HLWH-1TTM25-MF-BK - 1420921

Technical data

Ambient conditions


| | |
|---------------------------------|-------------------|
| | 12 (UL 50e) |
| Ambient temperature (operation) | -40 °C ... 125 °C |

General


| | |
|------------------------------|---|
| Note | For contact inserts HC-B16, BB32, D40, DD72, HS6, HV6, M, K |
| Size | B16 |
| Housing type | Sleeve housing |
| Locking type | Screw locking |
| Fixing screws | M6 (screw head: 5 mm Allen screw) |
| No. of cable outlets | 1 |
| Cable exit | straight |
| Screw connection | none |
| Type of the screw connection | 1x M25 |
| Housing material | Die-cast aluminum, salt water resistant |
| Housing surface material | Powder-coated, black |
| Seal material | Viton |
| Material lock | Stainless steel |

Drawings

Dimensional drawing



Dimensional drawing



Mounting cutout

¹⁾ when M4 screws are used

²⁾ when self-tapping Torx® screws are used (Torx® 20, M4)

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.1 | 27261203 |
| eCl@ss 8.0 | 27440202 |
| eCl@ss 9.0 | 27440202 |

Housing - HC-ADV-B16-HLWH-1TTM25-MF-BK - 1420921

Classifications

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC000437 |
| ETIM 6.0 | EC000437 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 31261501 |
|-------------|----------|

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|--|---------------------|
| EAC | | 7500651.22.01.00246 |
|-----|--|---------------------|

Accessories

Accessories

Full screw connection

Cable gland - HC-K-KV-M25(11-17) - 1690639



Plastic screw connection up to 5 bar, thread length: 8 mm, cable diameter: 11 - 17 mm, WAF 29, screw connection: M25

Housing - HC-ADV-B16-HLWH-1TTM25-MF-BK - 1420921

Accessories

Cable gland - HC-M-KV-M25(14-21) - 1646007



Metal screw connection up to 5 bar, thread length: 7 mm, cable diameter: 14 - 21 mm, WAF 34, screw connection: M25

Cable gland - HC-EMV-KV-M25(9-16,5) - 1690516



EMC screw connection up to 5 bar, thread length: 7.5 mm, cable diameter: 9.0 - 16.5 mm, WAF 29, screw connection: M25

Cable gland - HC-M-KV-M25(1ASI) - 1584020



Metal screw connection for an AS-Interface flat-ribbon conductor, thread type M25

Cable gland - G-INS-M25-M68N-NNES-S - 1411165



Cable gland, Cable gland material: Nickel-plated brass, External cable diameter 11 mm ... 17 mm, Shielding: No, Connecting thread: M25, Color: silver

Labeled device marker

Plastic label - US-EMLP (20X9) CUS - 0830085



Plastic label, can be ordered: By card, white, labeled according to customer specifications, Mounting type: Adhesive, Lettering field: 20 x 9 mm

Housing - HC-ADV-B16-HLWH-1TTM25-MF-BK - 1420921

Accessories

Multiple screw connection

Cable gland - HC-M-KV-M25(1X10/1X11) - 1580228



Special cable screw connection M25, brass nickel-plated, grommet with 10 mm and 11 mm holes

Panel mounting flange

Mounting flange - HC-B-AF - 1686533



Panel mounting flange for HEAVYCON-ADVANCE TMS housing with screw locking

Mounting flange - HC-B-AF-SET - 1604638



Panel mounting flange for screw locking, set comprising 2 panel mounting flanges with 4 self-tapping screws (M4, Torx[®]) and 4 fan-type washers

Protective cover

Protective covers - HC-B 16-TMS-SD-IP50 - 1690752



Protective cover B16, Clip locking, Protective cover material: PA, Seal: no, With lanyard, Diameter of retaining cord eyelet: 4 mm

Screwdriver tools

Housing - HC-ADV-B16-HLWH-1TTM25-MF-BK - 1420921

Accessories

Screwdriver - SF-BIT-HEXB 5-89 - 1208911



Screw bit, hexagonal with ball head, E6.3-1/4" drive, size: Hex 5 x 89 mm, hardened, suitable for holder according to DIN 3126-F 6.3/ISO 1173

Screwdriver - SF-M BH - 1212070



Bit screwdriver, with 1/4" quick-action chuck, handle length 119 mm, 2-component handle, with non-slip grip, suitable for bits according to DIN 3126-C 6.3 and E 6.3/ISO 1173, magnetic
