

## Contact insert module - HC-M-DSUB-09-UT-M - 1423723


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Contact insert module, Type: D-SUB-9, Pin, Screw connection, 50 V, 1 A, 0.08 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, Application: Data

RoHS

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 369419
GTIN	4055626369419
Custom tariff number	85366990
Country of origin	China

### Technical data

#### Electrical characteristics

Note	For HEAVYCON housing type B6 to B48, HC-M-B...MF-... module carrier frame required
Rated voltage (III/3)	50 V
Rated current	1 A
Rated surge voltage	0.8 kV

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### Mechanical characteristics

Conductor cross section	0.08 mm <sup>2</sup> ... 0.5 mm <sup>2</sup>
Connection cross section AWG	28 ... 20
Stripping length of the individual wire	3.5 mm
Tightening torque	0.03 Nm ... 0.05 Nm

## Contact insert module - HC-M-DSUB-09-UT-M - 1423723

### Technical data

#### Mechanical characteristics

Insertion/withdrawal cycles	≥ 500
Minimum housing height	72 mm

#### General

Type	D-SUB-9
Series	HC-M-DSUB
Number of module slots	1
Connection method	Screw connection
Flammability rating according to UL 94	V0
Degree of pollution	3
Overvoltage category	III

#### Material data

Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----