

# Housing - HC-STA-D25-SLWS-2SSM20-EL-AL - 1424392


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Box mounting bases D25, With single locking latch, Material: Die-cast aluminum, salt water resistant, Cable outlets: 2, lateral, Height: 57 mm, Cable gland: none, Gland: no, 2x M20, Standard



## Key Commercial Data

Packing unit	1
GTIN	 4 055626 371320
GTIN	4055626371320

## Technical data

### Dimensions

Height	57 mm
Width	51 mm
Length	80 mm

### Ambient conditions

Degree of protection of housing (IP)	IP66
	IP67
Degree of protection of housing (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C

### General

Size	D25
Housing type	Box mounting bases

## Housing - HC-STA-D25-SLWS-2SSM20-EL-AL - 1424392


### Technical data

#### General

Color	silver
Locking type	With single locking latch
No. of cable outlets	2
Cable exit	lateral
Screw connection	none
Type of the screw connection	2x M20
Housing material	Die-cast aluminum, salt water resistant
Material lock	PA

### Drawings

Dimensional drawing



Dimensional drawing