

# Housing - HC-STA-D25-SLWSC-2SSM25-EL-AL - 1424397

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Box mounting bases D25, With single locking latch, Material: Die-cast aluminum, salt water resistant, Protective cover material: Polycarbonate, Cable outlets: 2, lateral, Height: 57 mm, Cable gland: none, Gland: no, 2x M25, Protective cover: Yes, Standard



## Key Commercial Data

Packing unit	1
GTIN	
GTIN	4055626371375

## Technical data

### Dimensions

Height	57 mm
Width	51 mm
Length	80 mm

### Ambient conditions

Degree of protection of housing (IP)	IP66
	IP67
Degree of protection of housing (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C

### General

Size	D25
Housing type	Box mounting bases

# Housing - HC-STA-D25-SLWSC-2SSM25-EL-AL - 1424397


## Technical data

### General

Color	silver
Locking type	With single locking latch
No. of cable outlets	2
Cable exit	lateral
Screw connection	none
Type of the screw connection	2x M25
Protective cover	Yes
Housing material	Die-cast aluminum, salt water resistant
Material lock	PA
Material, protective cover	Polycarbonate

## Drawings

Dimensional drawing



Dimensional drawing

## Classifications

eCl@ss

eCl@ss 5.1	27143424
eCl@ss 6.0	27261203
eCl@ss 7.0	27440202
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

ETIM

ETIM 5.0	EC000437
----------	----------