

Cable gland - G-INVEN-M12-M67N-PNES-BK - 1424535

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Cable gland material: PA, External cable diameter 4 mm ... 8 mm, Shielding: No, Connecting thread: M12

Product Description

Cable gland with pressure compensation element and flat gasket

Why buy this product

- reduces the formation of condensation
-

Key Commercial Data

Packing unit	1
GTIN	
GTIN	4055626374406
Custom tariff number	39269097

Technical data

Dimensions

Length	33 mm
Wrench size, union nut	19 mm
Wrench size, support	19 mm
Length of the connecting thread	8 mm
Feed-through hole diameter	12.1 mm ... 12.2 mm
External cable diameter	4 mm ... 8 mm
	4 mm ... 8 mm (for UL 514 B)

Cable gland - G-INVEN-M12-M67N-PNES-BK - 1424535

Technical data

Ambient conditions

Degree of protection	IP67
	IP66
Ambient temperature (operation)	-20 °C ... 100 °C (static)

General


Cable gland material	PA
Cable seal material	CR
Shielded	No
Thread type on connection side	M12
Thread pitch	1.5 mm
Torque	2 Nm (Union nut)
	2 Nm (Support)
	2 Nm (for UL514 B: union nut / support)
Flammability rating according to UL 94	V2
Impact category	5
Execution of the strain relief	A
Manufacturer	BIMED
Manufacturer Designation	BMVG-2S

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Drawings

Dimensional drawing



Dimensional drawing

Approvals

Approvals

Cable gland - G-INVEN-M12-M67N-PNES-BK - 1424535





Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E199260
cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E199260
EAC			EAC-Zulassung
cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	
