

Cable gland - G-INVEN-M20-M67N-NNES-S - 1424540

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Cable gland material: Nickel-plated brass, External cable diameter 6 mm ... 12 mm, Shielding: No, Connecting thread: M20, Color: silver


Product Description

Cable gland with pressure compensation element and flat gasket

Why buy this product

- reduces the formation of condensation
-

Key Commercial Data

| | |
|----------------------|---|
| Packing unit | 1 |
| GTIN |  4 055626 374451 |
| GTIN | 4055626374451 |
| Custom tariff number | 39269097 |

Technical data

Dimensions

| | |
|---------------------------------|-------------------------------|
| Length | 35 mm |
| Wrench size, union nut | 22 mm |
| Wrench size, support | 22 mm |
| Length of the connecting thread | 8 mm |
| Feed-through hole diameter | 25.1 mm ... 25.2 mm |
| External cable diameter | 6 mm ... 12 mm |
| | 6 mm ... 12 mm (for UL 514 B) |

Cable gland - G-INVEN-M20-M67N-NNES-S - 1424540

Technical data

Ambient conditions


| | |
|---------------------------------|----------------------------|
| Degree of protection | IP67 |
| | IP66 |
| Ambient temperature (operation) | -20 °C ... 100 °C (static) |

General

| | |
|--------------------------------|---|
| Cable gland material | Nickel-plated brass |
| Cable seal material | CR |
| Shielded | No |
| Thread type on connection side | M20 |
| Thread pitch | 1.5 mm |
| Torque | 7.5 Nm (Union nut) 7.5 Nm (Support) 7.5 Nm (for UL514 B: union nut / support) |
| Color | silver |
| Impact category | 5 |
| Execution of the strain relief | A |
| Manufacturer | BIMED |
| Manufacturer Designation | BMBCVG-02 |

Drawings

Dimensional drawing



Dimensional drawing

Approvals

Approvals

Approvals





UL Recognized / cUL Recognized / EAC / cULus Recognized

Cable gland - G-INVEN-M20-M67N-NNES-S - 1424540

Approvals

Ex Approvals

Approval details

| | | | |
|------------------|---|---|---------------|
| UL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | E199260 |
| cUL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | E199260 |
| EAC |  | | EAC-Zulassung |
| cULus Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | |
