

Cable gland - G-INS-M20-M68N-SNES-S - 1424543

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Cable gland material: Stainless steel 1.4305, External cable diameter 6 mm ... 12 mm, Shielding: No, Connecting thread: M20, Color: silver



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 374482
GTIN	4055626374482
Custom tariff number	73181639
Country of origin	Turkey

Technical data

Dimensions

Length	33 mm
Wrench size, union nut	22 mm
Wrench size, support	22 mm
Hexagon angular dimension	24.5 mm
Length of the connecting thread	8 mm
Feed-through hole diameter	20.1 mm ... 20.3 mm
External cable diameter	6 mm ... 12 mm
	10 mm ... 12 mm (for UL 514 B)

Ambient conditions

Degree of protection	IP68 (5 bar, 30 min.)
	IP66
	IP69

Cable gland - G-INS-M20-M68N-SNES-S - 1424543

Technical data

Ambient conditions


Ambient temperature (operation)	-20 °C ... 100 °C (static)
---------------------------------	----------------------------

General

No. of conductors	1
Cable gland material	Stainless steel 1.4305
Material, insert	Polyamide 6
Cable seal material	Neoprene
Shielded	No
Thread type on connection side	M20
Thread pitch	1.5 mm
Torque	8 Nm (Union nut)
	8 Nm (Support)
	6 Nm (for UL514 B: union nut / support)
Color	silver
Impact category	2
Execution of the strain relief	A
Assembly instructions	1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque
Manufacturer	BIMED
Manufacturer Designation	BMSC-02

Drawings

Dimensional drawing



Dimensional drawing

Approvals

Approvals

Cable gland - G-INS-M20-M68N-SNES-S - 1424543




Approvals

Approvals

UL Listed / cUL Listed / EAC / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E199260
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E199260
EAC			EAC-Zulassung
cULus Listed	