

## Adapter - HC-B-TA-PG29-PLR-BK - 1414250

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Adapter, plastic, for EVO housing, Pg 29 thread



### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 022130
GTIN	4055626022130
Weight per Piece (excluding packing)	40.000 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Length of internal thread	12 mm
---------------------------	-------

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

#### General

Material	PA
Housing material	PA
Thread type on connection side	Bayonet B plastic
Thread type on seal side	Pg29
Torque	10 Nm (Tightening torque of screw connection to be screwed in)
Flammability rating according to UL 94	V0

# Adapter - HC-B-TA-PG29-PLR-BK - 1414250

## Technical data

### General

Assembly instructions	Bayonet locking max. 3x can be removed
-----------------------	--

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Approvals

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		7500651.22.01.00246
-----	---	---------------------

---