

Cable gland - G-INB-M16-S68N-PEPDS-LG - 1415172

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Application: Standard, External cable diameter 4.5 mm ... 10 mm, Shielding: No, Connecting thread: M16, Color: light gray, with bend protection sleeve

The figure shows version G-INB-M25-M68N-PEPDS-LG

Why buy this product

- Glow-wire test: 750°C
- Weatherproof sealing material
- Halogen-free

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
GTIN	 4 055626 038049
GTIN	4055626038049
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length	82 mm
Wrench size, union nut	20 mm
Wrench size, support	20 mm
Hexagon angular dimension	22 mm
Length of the connecting thread	9 mm

Cable gland - G-INB-M16-S68N-PEPDS-LG - 1415172

Technical data

Dimensions

Feed-through hole diameter	16.1 mm ... 16.2 mm
External cable diameter	4.5 mm ... 10 mm
	6 mm ... 8.6 mm (for UL 514 B)

Ambient conditions


Degree of protection	IP68 (5 bar / 0.5 h)
	IP69 (DIN EN 60529 / IEC 60529)
Ambient temperature (operation)	-40 °C ... 100 °C (static)

General

No. of conductors	1
Shielded	No
Thread type on connection side	M16
Thread pitch	1.5 mm
Torque	3 Nm (Union nut)
	3.5 Nm (Support)
Color	light gray
Impact category	2
Execution of the strain relief	A
Manufacturer	WISKA
Manufacturer Designation	ESKVS 16

Drawings

Dimensional drawing



Approvals

Approvals

Cable gland - G-INB-M16-S68N-PEPDS-LG - 1415172





Approvals

Approvals

UL Recognized / cUL Recognized / GOST-R / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E179850
cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E179850
GOST-R			POCC DE.A*98.H12052
cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	
