

## Contact insert module - HC-M-02-CT-F-HV-16 - 1417407

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON contact insert module, female, 2-pos. to 5000 V, crimp connection



### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 112725
GTIN	4055626112725
Weight per Piece (excluding packing)	60.000 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Height	33.9 mm
Width	34.1 mm
Length	29.3 mm

#### Electrical characteristics

Note	For HEAVYCON housing type B6 to B48, HC-M-B...MF... hinged module carrier frame required, CK2,5-ED... imp contacts, crimp contacts not supplied as standard.
Rated voltage (III/3)	2900 V (Conductor-PE)
	5000 V (Conductor-Conductor)
Rated current	16 A
Rated surge voltage	15 kV

# Contact insert module - HC-M-02-CT-F-HV-16 - 1417407

## Technical data

### Electrical characteristics

Connection profile	2
--------------------	---

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

### Mechanical characteristics

Conductor cross section	0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Connection cross section AWG	20 ... 12
Stripping length of the individual wire	9.5 mm
Wire diameter	2.5 mm
Wire diameter including insulation	8 mm
Insertion/withdrawal cycles	≥ 500
Minimum housing height	72 mm

### General

Series	HC-M-HV
Number of module slots	2
Connection method	Crimp connection
Flammability rating according to UL 94	V0
Degree of pollution	3
Overvoltage category	III
Assembly instructions	Use HC housing h ≥ 72 mm. Plug-in connections may only be operated only when there is no load/voltage.
Connection	<p>Assembly procedure:</p> <ul style="list-style-type: none"> <li>- Strip wire 9.5 mm,</li> <li>- connect the stripped part of the wire through the locking sleeve (for wire diameter &gt; 3.2 mm),</li> <li>- crimp wire (with protracted locking sleeve) with CK2.5...ED crimp contact,</li> <li>- lock the locking sleeve with the crimp contact together with the module's insulating body.</li> </ul>

### Material data

Contact material	Copper alloy
Contact surface material	Ag (alternatively Au)
Contact carrier material	PC / PTFE


### Standards and Regulations

Flammability rating according to UL 94	V0
--	----


## Drawings

# Contact insert module - HC-M-02-CT-F-HV-16 - 1417407


Schematic diagram



Dimensional drawing



Diagram



## Approvals

Approvals

Approvals

EAC / CSA / UL Recognized

Ex Approvals

## Approval details

EAC		7500651.22.01.00246
-----	--	---------------------


CSA		<a href="http://www.csagroup.org/services/testing-and-certification/certified-product-listing/">http://www.csagroup.org/services/testing-and-certification/certified-product-listing/</a>	13631
-----	--	---	-------

mm <sup>2</sup> /AWG/kcmil	12
----------------------------	----

## Contact insert module - HC-M-02-CT-F-HV-16 - 1417407

### Approvals

Nominal current IN	24 A
Nominal voltage UN	600 V

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	E118976
mm <sup>2</sup> /AWG/kcmil		12	
Nominal current IN		28 A	
Nominal voltage UN		600 V	