

## Housing - HC-STA-D07-HHFS-1SGM20-PL-BK - 1419257


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing D7, for single locking latch, Material: PA, Cable outlets: 1, lateral, Height: 54.5 mm, Cable gland: with, Gland: no, 1x M20, Standard



### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 159980
GTIN	4055626159980
Weight per Piece (excluding packing)	20.000 g
Custom tariff number	85389099
Country of origin	China

### Technical data

#### Dimensions

Height	54.5 mm
Width	59.8 mm
Length	26.5 mm
External cable diameter	4 mm ... 10 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP66
Degree of protection of housing (NEMA)	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	for contact inserts HC-A03, A04, D07, D08, Q02, Q03, Q04, Q05, Q07, Q12
------	---

# Housing - HC-STA-D07-HHFS-1SGM20-PL-BK - 1419257


## Technical data

### General

Size	D7
Housing type	Sleeve housing
Color	black
Locking type	for single locking latch
No. of cable outlets	1
Cable exit	lateral
Screw connection	with
Type of the screw connection	1x M20
Housing material	PA
Material lock	PA

## Drawings

Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 5.1	27269202
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

### ETIM

ETIM 5.0	EC000437
ETIM 6.0	EC000437

### UNSPSC

UNSPSC 13.2	31261501
-------------	----------

## Approvals

### Approvals

## Housing - HC-STA-D07-HHFS-1SGM20-PL-BK - 1419257

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		EAC-Zulassung
-----	---	---------------

### Accessories

Accessories

Labeled device marker

Plastic label - US-EMLP (20X9) CUS - 0830085



Plastic label, can be ordered: By card, white, labeled according to customer specifications, Mounting type: Adhesive, Lettering field: 20 x 9 mm