

Housing - HC-STA-D50-SHWD-2SSP21-ELC-AL - 1424415


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Box mounting bases D50, With double locking latch, Material: Die-cast aluminum, salt water resistant, Cable outlets: 2, lateral, Height: 82 mm, Cable gland: none, Gland: Yes, 2x Pg21, Standard



Key Commercial Data

Packing unit	1
GTIN	 4 055626 371559
GTIN	4055626371559

Technical data

Dimensions

Height	82 mm
Width	70 mm
Length	106 mm

Ambient conditions

Degree of protection of housing (IP)	IP66
	IP67
Degree of protection of housing (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C

General

Size	D50
Housing type	Box mounting bases

Housing - HC-STA-D50-SHWD-2SSP21-ELC-AL - 1424415


Technical data

General

Color	silver
Locking type	With double locking latch
No. of cable outlets	2
Cable exit	lateral
Screw connection	none
Type of the screw connection	2x Pg21
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	Uncoated
Material lock	PA
Assembly instructions	One opening is sealed with a plastic filler plug and can be opened using a screwdriver.

Drawings

Dimensional drawing



Dimensional drawing