

## Panel feed-through - Q 1,5/4A50/24-M20KU-ESA-ASI BK - 1437274

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Panel feed-through with QUICKON fast connection technology, for accommodating one or two AS-i flat-ribbon conductors, on the rear side with four 0.5 m long individual wires 1.5 mm<sup>2</sup>



### Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	60.000 g
Custom tariff number	85444290
Country of origin	Poland

### Technical data

#### Dimensions

Length of cable	0.5 m
Stripping length of the sheath	40 mm

#### Ambient conditions

Degree of protection	IP65
	IP67

#### General

Number of positions	4
Overvoltage category	III
Degree of pollution	3
Connection method	QUICKON fast connection

#### Material

Contact material	Copper alloy
Contact surface material	Pre-nickel plated and tin-plated

# Panel feed-through - Q 1,5/4A50/24-M20KU-ESA-ASI BK - 1437274

## Technical data

### Material

Contact carrier material	PA
--------------------------	----

### Characteristics head 2


Color	black
-------	-------

### Standards and Regulations

Connection in acc. with standard	CUL
----------------------------------	-----

## Drawings

Dimensional drawing



## Approvals

### Approvals

---

### Approvals

UL Recognized / cUL Recognized / VDE Zeichengenehmigung / EAC / cULus Recognized

---

### Ex Approvals


---


### Approval details

UL Recognized <a href="http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm</a> FILE E 118976	
Nominal current I <sub>N</sub>	15 A
Nominal voltage U <sub>N</sub>	250 V


## Panel feed-through - Q 1,5/4A50/24-M20KU-ESA-ASI BK - 1437274

### Approvals

cUL Recognized  <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> FILE E 118976	
Nominal current IN	11 A
Nominal voltage UN	250 V

VDE Zeichengenehmigung  <a href="http://www.vde.com/en/Institute/OnlineService/VDE-approved-products/Pages/Online-Search.aspx">http://www.vde.com/en/Institute/OnlineService/VDE-approved-products/Pages/Online-Search.aspx</a> 40032336	
mm <sup>2</sup> /AWG/kcmil	0.75-1.5
Nominal voltage UN	500 V

EAC EAC-Zulassung
-------------------

cULus Recognized  <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	
--	--