

Protective covers - HC-B 32-TMS-SD-IP65 - 1580539


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON ADVANCE B32 IP65 protective cover, for panel mounting side, screw locking with 2 Allen screws, with seal, 3 mm retaining cord eyelet



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	6 pc
GTIN	 4 046356 463355
GTIN	4046356463355
Weight per Piece (excluding packing)	93.340 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-20 °C ... 100 °C

General

Size	B32
Type	HC-ADVANCE protective cover
Housing type	Protective cover
Color	gray
Locking type	Screw locking
Torque	3 Nm (Locking screw)
Fixing screws	M6 (5 mm Allen screw)

Protective covers - HC-B 32-TMS-SD-IP65 - 1580539

Technical data

General

Seal material	NBR
Material lock	Stainless steel
Material of locking screw	Stainless steel
Material, protective cover	PA
Flammability rating according to UL 94	V0

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27149110
eCl@ss 5.1	27149100
eCl@ss 6.0	27261200
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002314
ETIM 5.0	EC002314
ETIM 6.0	EC002314

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121421